

Ford Cup

■ Introduction:

It is designed according to ASTM D1200, D333 and D365 standards and widely used to measure the viscosity of paints, inks, lacquers and other liquids.



■ Technical info:

- ◆ Volume: 100 ml
- ◆ Material: Cup body-aluminum alloy;
Nozzle-stainless steel

■ Order info:

Order No.	Orifice(mm)	Viscosity Range(cSt)	Flow Time(sec)
BEVS 1101/1	2.1	10-35	55-100
BEVS 1101/2	2.8	25-120	40-100
BEVS 1101/3	3.4	49-220	30-100
BEVS 1101/4	4.1	70-370	30-100
BEVS 1101/5	5.8	200-1200	30-100