

Laboratory Mixer

■ Introduction:

BEVS 2501 series Laboratory Mixer adopts frequency-adaptor to adjust speed with the advanced touch-screen control design. It can disperse, mix and grind various liquids. User can set speed and running time. It's a good choice for R&D and QC purposes.



BEVS 2501/S(lite version)



BEVS 2501/1



BEVS 2501/1L, 2L



BEVS 2501/2A,3A



BEVS 2501/5A

■ Application:

It is widely used in industries including coatings, dyes, inks, pigments, papermaking, cosmetics, food, resins, adhesives, emulsions, medicine, petroleum, pesticides, daily chemicals and others.



Vessel



Dispersing disc




Milling disc

■ Technical info:


■ Technical info:



Touch control



Adjustable speed



Adjustable dispersing time



Height adjustment



Max. capacity: 20L, model 5A



Frequency modulation motor



100-230V, 50/60HZ



Auto/Manual lifting



Clamping sensor



Extra long shaft(modle L/A series)

■ Order info:

Model	Power(w)	RPM	Lifting stroke (mm)	Lifting	Vessel supported(L)
BEVS 2501/S	550	30-9000	210	Manual	1.5/3.0
BEVS 2501/1	550	30-9000	250	Manual	0.5/1.5
BEVS 2501/1L	550	30-9000	250	Manual	0.5/1.5
BEVS 2501/2L	750	60-6000	280	Manual	0.5/1.5
BEVS 2501/2A	750	60-6000	280	Auto	1.5/3/5
BEVS 2501/3A	1100	60-5500	330	Auto	3/5/10
BEVS 2501/5A	1500	60-6000	400	Auto	5/10/20

■ Standard comes with 3 discs. L-extra long shaft, A-auto lift.

■ “ Vessel supported ” refers only to the types of vessels compatible with the mixer, and does not indicate the vessel included in the standard configuration. If you wish to confirm which vessel is included with a specific mixer, please contact us before placing your order.

■ Accessory info:

Dispersing disc:

Model	Diameter(mm)	Material
BEVS 2501/1	35	Stainless steel
BEVS 2501/2	50	
BEVS 2501/3	60	
BEVS 2501/4	80	
BEVS 2501/5	100	
BEVS 2501/6	120	
BEVS 2501/7	150	
BEVS 2501/8	200	

Disc dia. 30 and 40 mm are also available.

Milling disc:

Model	Diameter(mm)	Material
BEVS 2501/P/025	45	Nylon
BEVS 2501/P/026	60	
BEVS 2501/P/027	45	Teflon
BEVS 2501/P/028	60	

Vessel:

Model	Capacity(l)	Material
BEVS 2511/1	0.5	Double wall stainless steel
BEVS 2511/2	1.5	
BEVS 2511/3	3	
BEVS 2511/4	5	
BEVS 2511/5	10	
BEVS 2511/6	20	